



BUILDING ENTRANCE TERMINAL SOLUTION

Project Name: _____ Date: _____
 Customer: _____ Telephone: _____
 Sales Contact: _____ Fax: _____

Basic Considerations

Application

- Indoor
 Indoor/Outdoor
 Outdoor

Pair Count

- 25 50 100
 Other _____

Protector Block Receptacle Plating

- Tin Gold
(Recommended to match 5-pin plating)

Input Options

- Stubless
 Stub
 Gauge
 22 24 26
 Other _____
 Length _____
 Splice Chamber
 MS² 710 raw ended
 IDC
 Tool-less 66 Block
 MOXSTM 110
 Other _____

Output Options

- Stubless
 Stub
 Gauge
 22 24 26
 Other _____
 Length _____
 IDC
 Tool-less 110
 MOXSTM RJ-21
 66 Block
 Other _____

Protector Options

- 5-Pin
 Gas Tube
 Solid-State
 220 V 300 V
 Heat Coil
 none 150 mA 350 mA
 PTC
 Plating Option
 Tin Gold
 Qty _____
- 4-Pin (Canada only)
 Gas Tube
 Solid-State
 220 V 300 V
 Heat Coil
 none 150 mA 350 mA
 PTC
 Qty _____

Subscriber Demarcation

- 8925 Block (RJ-11 Test Jack)

Description of Solution: _____

Accessories

- Please Describe _____



