

AnyLAN™ Integrated 1U Housing

A LANscape®
Solutions Product

features and benefits |

Compatible with Plug & Play™ AnyLAN™ solutions	Allows for easier installation and moves, adds and changes (MACs)
Factory terminated	Eliminates need for field termination, improving reliability and speed of deployment
Available in 12-48 fiber, single-mode and multi-mode, with ST®, SC and LC connectivity	Network flexibility

Corning Cable Systems AnyLAN Integrated 1U housing utilizes the AnyLAN OptiTip® adapter with a 1U rack-mountable housing for quick and easy deployment, eliminating the need for field-terminated and strain-relieved fiber optic cables. The housing is fully compatible with existing Plug & Play AnyLAN solutions and is ideal for star, ring, point-to-point or zone architectures. The factory-terminated housing provides industry-leading quality and reliability, while eliminating the time required for field-termination methods.



AnyLAN Integrated 1U Housing, 24 fiber (front)
| Photo LAN1757



AnyLAN Integrated 1U Housing, 24 fiber (rear)
| Photo LAN1758

specifications |

Dimensions (H x W x D) cm (in)	Shipping Weight kg (lb)
4.4 x 45.5 x 24.6 (1.75 x 17.9 x 9.7)	2 (4.4)

AnyLAN™ Integrated 1U Housing

A LANscape®
Solutions Product

ordering information |

CC1 - OT - H
|1 |2 |1 |3

|1

Select fiber count.

- 12 = 12 fibers,
all adapter types
- 24 = 24 fibers,
all adapter types
- 36 = 36 fibers, SC duplex
- 48 = 48 fibers, LC duplex

|2

Select fiber type.

- R = Single-mode
- S = 50 µm multimode (OM3)
- C = 50 µm multimode (OM2)

|3

Select adapter code.

SC Duplex (12, 24 and 36 fibers)

- 59 = Single-mode
- E7 = 50 µm multimode (OM3)
- G7 = 50 µm multimode (OM2)

ST® Compatible (12 and 24 fibers)

- 6T = Single-mode
- H3 = 50 µm multimode (OM3)
- G5 = 50 µm multimode (OM2)

LC Duplex (12, 24 and 48 fibers)

- A9 = Single-mode
- E4 = 50 µm multimode (OM3)
- D3 = 50 µm multimode (OM2)



AnyLAN Integrated 1U Housing, 24 fiber
| Photo LAN1760



AnyLAN Integrated 1U Housing, 24 fiber
| Photo LAN1761

Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/cablesystems

Corning Cable Systems reserves the right to improve, enhance and modify the features and specifications of Corning Cable Systems products without prior notification. LANscape and OptiTip are registered trademarks of Corning Cable Systems Brands, Inc. AnyLAN and Plug & Play are trademarks of Corning Cable Systems Brands, Inc. ST is a registered trademark of Lucent Technologies. All other trademarks are the properties of their respective owners. Corning Cable Systems is ISO 9001 certified. © 2009, 2010 Corning Cable Systems. All rights reserved. Published in the USA. LAN-1215-EN / June 2010