

	Representative microplate (Corning Cat. #)	Well Volume (uL)	Well Depth (mm)	Well Diameter (top/bottom)	Plate Length (mm)	Plate Width (mm)	Plate Height (mm)	A1 Row Offset	A1 Column Offset	Well center to well center spacing	Flange or skirt height (mm)	Stack Height	Well Bottom Elevation	Well Bottom Thickness	Well Bottom Area	Distance to bottom of plate
1536 Well Microplates																
1536 well solid, round bottom	3936, 3937	10	5.01	1.69 / 0.74	127.8	85.5	10.4	7.86	11.0	2.25	2.16	8.7	5.41	0.9	N/A	4.49
1536 well black w/ clear bottom	3891, 3893	12.8	4.8	1.8 / 1.63	127.8	85.5	10.4	7.86	11.0	2.25	2.16	8.9	5.6	0.076	0.0209	5.524
1536 2 uL "wafer" plate	3851, 3852, 3853, 3854, 3855, 3857, 3858	2	1.5	1.19 / 1.50	127.8	85.5	3.81	7.86	11.01	2.25	3.17	3.05	2.31	1.04	0.01884	1.27
1536 well solid flat bottom	3724, 3725, 3726, 3727, 3728, 3729	12.8	4.8	1.8 / 1.63	127.8	85.5	10.4	7.86	11.0	2.25	2.16	8.9	5.6	0.076	0.0209	5.524
1536 well Echo™ Qualified	3730	12.5	4.95	1.70 / 1.53	127.8	85.5	10.4	7.86	11.01	2.25	2.16		5.45	0.75		4.7

A1 Row Offset (mm) = Distance from top of plate

Note: For additional microplate information, please visit our web site www.corning.com/lifesciences or contact us at 1-978-635-2200 (1-800-492-1110 for U.S. customers)

*Does not include V portion