













### LIQUID HANDLING - Microplate Washers

Company Name	Product Name	Image	Microplate Formats			Manifold	Programmable Features			Optional Plate Stacker	Stacker Capacity	Integratable
			96	384	1536		Dispense Volume (µL/well)	Maximum Soak Time (seconds)	Shake Time (seconds)			
Anthos Labtec	Fluido		Yes	Yes	No	8, 12, 16	50-2000	1000	10	No	N/A	Yes
Bio-Tek® Instruments, Inc.	ELx405™		Yes	Yes	No	96/192	25-3000	600	User Defined	Yes	30 Plates	Yes
Bio-Tek Instruments, Inc.	ELx50™		Yes	Yes	No	8, 12, 16	25-3000	600	0-600	No	N/A	No
Flush Tec div. of DI	Flusher™		Yes	Yes	No	8, 12	12.5-3000	999x2	No	No	No	Yes
Flush Tec div. of DI	Tall-Flusher 96™		Yes	No	No	8, 12	50-3000	999x2	No	No	No	Yes
Flush Tec div. of DI	Tall-Washer 96™		Yes	No	No	8, 12	50-3000	999x2	No	No	No	Yes


### LIQUID HANDLING - Microplate Washers

Company Name	Product Name	Image	Microplate Formats			Manifold	Programmable Features			Optional Plate Stacker	Stacker Capacity	Integratable
			96	384	1536		Dispense Volume (µL/well)	Maximum Soak Time (seconds)	Shake Time (seconds)			
Labcyte	MiniGene Line Dispenser		Yes	Yes	No	8/16	5ul - 2ml	N/A	N/A	N/A	50 Plates	Yes
Molecular Devices Corporation	EMBLA 384		No	Yes	No	192	10-100	600	No	Yes	20/20	Yes
Molecular Devices Corporation	Skanska 300		Yes	No	No	96	50-350	170	No	Yes	25	No
Molecular Devices Corporation	Skanska Washer 300		Yes	No	No	96	50-350	170	No	No	N/A	Yes
Molecular Devices Corporation	Skanska Washer 400		Yes	No	No	96	50-350	170	No	No	N/A	Yes
Tecan Group Ltd.	96 PW™		Yes	No	No	96	50-3000	1-600	No	Yes	80	Yes

## LIQUID HANDLING - Microplate Washers

Company Name	Product Name	Image	Microplate Formats			Manifold	Programmable Features			Optional Plate Stacker	Stacker Capacity	Integratable
			96	384	1536		Dispense Volume (µL/well)	Maximum Soak Time (seconds)	Shake Time (seconds)			
Tecan Group Ltd.	Columbus™		Yes	No	No	8, 12, 16	50-400	1-999	1-999	No	N/A	Yes
Thermo Electron Corporation	Wellwash 4™		Yes	No	No	8, 12	0-750	600	No	No	N/A	Yes
Thermo Electron Corporation	Wellwash Ascent™		Yes	No	No	8, 12, 16, 24	50-1000	1200	Unlimited	Yes	108	Yes
Titertek®	M96 Series		Yes	No	No	96	50-500	Unlimited	Unlimited	S20	20	No
Titertek®	MAP Series		Yes	Yes	No	8, 16, 32, 96	Unlimited	Unlimited	Unlimited	S60	60	Yes
Tomtec	Quadra-Wash® 96/384		Yes	Yes	No	96, 384	10-350	99	No	Yes	25 or 50	No

### LIQUID HANDLING - Microplate Washers

Company Name	Product Name	Image	Microplate Formats			Manifold	Programmable Features			Optional Plate Stacker	Stacker Capacity	Integratable
			96	384	1536		Dispense Volume (µL/well)	Maximum Soak Time (seconds)	Shake Time (seconds)			
Tri Continent	Multiwash™ II		Yes	No	No	8, 12	50-400	250	No	No	N/A	No