

AnyLAN™ Integrated 1U Housing

A LANscape®
Solutions Product

features and benefits |

Compatible with Plug & Play™ AnyLAN™ solutions Allows for easier installation and moves, adds and changes

Factory terminated Eliminates need for field termination, improving reliability and speed of deployment

Available in 24-fiber, single-mode and multi-mode, with ST®, SC and LC connectivity Network flexibility

Corning Cable Systems AnyLAN Integrated 1U housing utilizes the AnyLAN OptiTip™ adapter with a 1U rack-mountable housing for quick and easy deployment, eliminating the need for field terminated and strain-relieved fiber optic cables. The housing is fully compatible with existing Plug & Play AnyLAN solutions and is ideal for star, ring, point-to-point or zone architectures. The factory-terminated housing provides industry leading quality and reliability, while eliminating the time required for field-termination methods.



AnyLAN Integrated 1U Housing (front)
| Photo LAN1757



AnyLAN Integrated 1U Housing (rear)
| Photo LAN1758

specifications |

Dimensions (H x W x D) cm (in)	Shipping Weight kg (lb)
4.4 x 45.5 x 24.6 (1.75 x 17.9 x 9.7)	2 (4.4)

AnyLAN™ Integrated 1U Housing

A LANscape®
Solutions Product

ordering information |

Part Number	Description
CC1-24OTR-2459H	1U Rack-Mountable Housing, 24 fibers, SC duplex adapters, single-mode fiber
CC1-24OTR-246TH	1U Rack-Mountable Housing, 24 fibers, ST® Compatible adapters, single-mode fiber
CC1-24OTR-24A9H	1U Rack-Mountable Housing, 24 fibers, LC duplex adapters, single-mode fiber
CC1-24OTS-24E7H	1U Rack-Mountable Housing, 24 fibers, SC duplex adapters, Pretium® 300 laser-optimized 50 µm fiber
CC1-24OTS-24H3H	1U Rack-Mountable Housing, 24 fibers, ST Compatible adapters, Pretium 300 laser-optimized 50 µm fiber
CC1-24OTS-24E4H	1U Rack-Mountable Housing, 24 fibers, LC duplex adapters, Pretium 300 laser-optimized 50 µm fiber
CC1-24OTC-24G7H	1U Rack-Mountable Housing, 24 fibers, SC duplex adapters, Pretium 150 laser-optimized 50 µm fiber
CC1-24OTC-24G5H	1U Rack-Mountable Housing, 24 fibers, ST Compatible adapters, Pretium 150 laser-optimized 50 µm fiber
CC1-24OTC-24D3H	1U Rack-Mountable Housing, 24 fibers, LC duplex adapters, Pretium 150 laser-optimized 50 µm fiber
CC1-24OTK-2491H	1U Rack-Mountable Housing, 24 fibers, SC duplex adapters, 62.5 µm fiber
CC1-24OTK-245TH	1U Rack-Mountable Housing, 24 fibers, ST Compatible adapters, 62.5 µm fiber
CC1-24OTK-24A8H	1U Rack-Mountable Housing, 24 fibers, LC duplex adapters, 62.5 µm fiber



AnyLAN™ Integrated 1U Housing
| Photo LAN1760



AnyLAN Integrated 1U Housing
| Photo LAN1761

Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA
800-743-2675 • FAX: 828-901-5973 • International: +1-828-901-5000 • www.corning.com/cablesystems

Corning Cable Systems reserves the right to improve, enhance and modify the features and specifications of Corning Cable Systems products without prior notification. LANscape and Pretium are registered trademarks of Corning Cable Systems Brands, Inc. AnyLAN, OptiTip and Plug & Play are trademarks of Corning Cable Systems Brands, Inc. ST is a registered trademark of Lucent Technologies. All other trademarks are the properties of their respective owners. Corning Cable Systems is ISO 9001 certified. © 2009 Corning Cable Systems. All rights reserved. Published in the USA. LAN-1215-EN / November 2009